

**Rittal – The System.**

Faster – better – everywhere.



# SG 2374.060

## Incandescent lamps

State: 24.06.2025 (Source: [rittal.com/bg-bg](http://rittal.com/bg-bg))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SG 2374.060 - Incandescent lamps for steady light components

With BA 15d base.

## Features

Model No.	SG 2374.060
Product description	With BA 15d base.
Benefits	Simple assembly and contact via bayonet fastener.
Function principle	A modular layout is possible with connection, optical and acoustic components, incandescent lamps and a label panel
Power consumption (approx.)	5 W
Rated impulse withstand voltage, phase to phase	28 V AC
Rated insulation voltage	2000 V AC
Rated operating voltage	24 V
Packs of	3 pc(s).
Net weight	0.024
Gross weight	0.026
Customs tariff number	85392198
EAN	4028177219885
ETIM 9	EC000232
ETIM 8	EC000232
ECLASS 8.0	27371220