

**Rittal – The System.**

Faster – better – everywhere.



**SZ 2562.300**

**Plastic gland plate**

State: 31.01.2026 (Source: [rittal.com/bg-bg](http://rittal.com/bg-bg))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SZ 2562.300 - Plastic gland plate with membranes, for AX

Simply pierce the plastic with a sharp object, and pull through the cable.

## Features

|  |   |
|--|---|
| Model No.                                    | SZ 2562.300   |
| Product description                          | Simply pierce the plastic with a sharp object, and pull through the cable.  |
| Material                                     | Plastic to UL 94-V0   |
| Colour                                       | Similar to RAL 7035   |
| Note   | The allocation of gland plate sizes is indicated on the relevant enclosures |
| Dimensions                                   | Width: 339 mm<br>Depth: 149 mm  |
| To fit                                       | Enclosure type: AX  |
| Gland plate                                  | Size: 2   |
| Protection category to IEC 60 529            | IP 66 if installed correctly  |
| Type rating to UL 50E                        | Type 1<br>Type 12   |
| No. of cable entries and Ø (mm)<br>min.-max. | 24 x 5-11<br>44 x 10-15<br>6 x 15-25<br>2 x 19-34<br>2 x 26-54              |
| Packs of                                     | 1 pc(s).  |
| Net weight                                   | 0.495   |
| Gross weight                                 | 0.5   |
| Customs tariff number                        | 39269097  |
| EAN  | 4028177935716   |
| E-Number Sweden                              | E3465289  |

## Features

---

ETIM 9 EC000211

---

ETIM 8 EC000211

---

ECLASS 8.0 27142421

## Approvals

---

Approvals UL + C-UL - FTTA