

# Rittal – The System.

Faster – better – everywhere.



## SZ 2562.400 Metal gland plate

State: 22.05.2026 (Source: [rittal.com/bg-bg](http://rittal.com/bg-bg))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SZ 2562.400 - Metal gland plate

As spare/replacement part for the standard gland plates supplied loose, IP 66 when mounting in the usual position at the bottom.

## Features

|                                   |   |
|-----------------------------------|---|
| Model No.                         | SZ 2562.400   |
| Design                            | solid   |
| Product description               | As spare/replacement part for the standard gland plates supplied loose.     |
| Material                          | Sheet steel   |
| Colour                            | RAL 7035  |
| Note                              | The allocation of gland plate sizes is indicated on the relevant enclosures |
| Dimensions                        | Width: 339 mm<br>Depth: 149 mm  |
| To fit                            | Enclosure type: AE  |
| Gland plate                       | Size: 4   |
| Protection category to IEC 60 529 | IP 66 when mounting in the usual position at the bottom                     |
| Packs of                          | 1 pc(s).  |
| Net weight                        | 0,5 kg  |
| Gross weight                      | 0,588 kg  |
| Customs tariff number             | 73079100  |
| ETIM 9                            | EC000211  |
| ETIM 8                            | EC000211  |
| ECLASS 8.0                        | 27142421  |
| Product description               | SZ Metal gland plate, closed, WD: 339x149 mm, size: 4                       |