

Rittal – The System.

Faster – better – everywhere.



SZ 2564.200

Plastic gland plate, modular

State: 23.05.2026 (Source: rittal.com/bg-bg)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 2564.200 - Plastic gland plate, modular with metric knockouts, for AX

Simply break through the plastic on the knockouts for cable glands. Additional rectangular cut-outs and reinforcement frame allow the cable gland to be installed directly (modular).



Features

| | |
|---|---|
| Model No. | SZ 2564.200 |
| Product description | Simply break through the plastic on the knockouts for cable glands. Additional rectangular cut-outs and reinforcement frame allow the cable gland to be installed directly (modular). |
| Material | Plastic to UL 94-V0 |
| Colour | RAL 7035 |
| Number of rectangular cutouts information | 1 rectangular cut-out can hold 10 small seal inserts |
| Number of rectangular cutouts | 6 |
| Note | The allocation of gland plate sizes is indicated on the relevant enclosures |
| No. of metric knockouts | 5 x M12 4 x M16 6 x M20 5 x M25 1 x M32 1 x M40 |

Features

| | |
|-----------------------------------|---|
| Dimensions | Width: 534 mm Depth: 149 mm |
| To fit | Enclosure type: AX |
| Gland plate | Size: 4 |
| Operating temperature range | -40 °C...80 °C |
| Protection category to IEC 60 529 | IP 66 if installed correctly |
| Type rating to UL 50E | Type 1 Type 12 |
| Packs of | 1 pc(s). |
| Net weight | 0,54 kg |
| Gross weight | 0,573 kg |
| Customs tariff number | 39269097 |
| ETIM 9 | EC000211 |
| ETIM 8 | EC000211 |
| ECLASS 8.0 | 27142421 |
| Product description | SZ Plastic gland plates, for AX, for cable entry, modular, pre-punched, WD: 534x149 mm, for gland plates size 4 |

Approvals

| | |
|-----------|------------------|
| Approvals | UL + C-UL - FTTA |
|-----------|------------------|