


# Rittal – The System.

Faster – better – everywhere.



## SZ 2566.300 Plastic gland plate

State: 22.05.2026 (Source: [rittal.com/bg-bg](http://rittal.com/bg-bg))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SZ 2566.300 - Plastic gland plate with membranes, for AX

Simply pierce the plastic with a sharp object, and pull through the cable.

## Features

Model No.	SZ 2566.300
Product description	Simply pierce the plastic with a sharp object, and pull through the cable.
Material	Plastic to UL 94-V0
Colour	Similar to RAL 7035
Note	The allocation of gland plate sizes is indicated on the relevant enclosures
Dimensions	Width: 401 mm Depth: 221 mm
To fit	Enclosure type: AX
Gland plate	Size: 6
Protection category to IEC 60 529	IP 66 if installed correctly
Type rating to UL 50E	Type 1 Type 12
No. of cable entries and Ø (mm) min.-max.	30 x 5-11 50 x 10-15 8 x 15-25 2 x 19-34 2 x 26-35 2 x 26-54 1 x 50-110
Packs of	1 pc(s).
Net weight	0,752 kg
Gross weight	0,76 kg
Customs tariff number	39269097
ETIM 9	EC000211

# Features

---

ETIM 8	EC000211
ECLASS 8.0	27142421
Product description	SZ Plastic gland plates, for AX, with membranes, WD: 401x221 mm, for gland plates size 6

# Approvals

---

Approvals	UL + C-UL - FTTA
-----------	------------------