## Rittal – The System.

Faster – better – everywhere.






# FT 2731.010 Viewing window

State: 05.11.2025 (Source: rittal.com/bg-bg)



## FT 2731.010 - Viewing window for AX

For external mounting on AX enclosures instead of a door and on surfaces.







#### **Features**

FT 2731.010
30 section
For external mounting on AX enclosures instead of a door and on surfaces.
Frame: Aluminium, natural anodised. Glass panel: Acrylic
Plastic handle with lock insert no. 3524 E
IP 54
1010.000
1054.000
1060.000
1360.000
Enclosure type: AX
Width: = 600 mm
Height: = 600 mm
Width: 597 mm
Height: 597 mm
Depth: 36 mm

© Rittal 2025

### **Features**

Visible area	Viewing window width: 537 mm Viewing window height: 537 mm
Build depth for components (max.)	32 mm
Packs of	1 pc(s).
Net weight	3.236
Gross weight	3.48
Customs tariff number	76101000
EAN	4028177938472
ETIM 9	EC002527
ETIM 8	EC002527
ECLASS 8.0	27182204

© Rittal 2025 3