



SK 3164.115 - Roof-mounted fans for VX, VX IT

Roof-mounted fan for the office sector with exceptionally low noise level (40 dB) and high volumetric flow (unimpeded air flow 1500 m³/h).



Features

Model No.	SK 3164.115
Benefits	Easy assembly, the roof plate variant eliminates the need to create mounting cut-outs Fully wired ready for connection
Material	Sheet steel, spray-finished
Colour	RAL 7035
Supply includes	Roof-mounted fans Assembly parts
Rated operating voltage	115 V, 1~, 50 Hz/60 Hz 110 V (DC)
Rated current max.	At 50 Hz: 0.6 A At 60 Hz: 0.7 A
Dimensions	Width: 511 mm Height: 227 mm Depth: 511 mm
IP protection category to IEC 60529	Internal circuit IP 54
Note	Reduction in the specified air throughput to 800 m ³ /h at 40 Pa counterpressure using two vented base/plinth trim panels
Operating temperature range	20 °C...55 °C

Features

Packs of	1 pc(s).
Net weight	18,445 kg
Gross weight	19,416 kg
Customs tariff number	84145915
ETIM 9	EC000320
ETIM 8	EC000320
ECLASS 8.0	27180716

Approvals

Certificates	EAC
Explanations	Declaration of conformity Declaration of conformity UK