



SK 3301.390 - Vertical shielding for VX IT, TS IT

To block the airflow on the left and right of the 482.6 mm (19") level, for enclosure height 2000 mm.

Features

| | |
|-----------------------|--|
| Model No. | SK 3301.390 |
| Design | Self-adhesive on one side |
| Product description | To block the airflow on the left and right of the 482.6 mm (19") level, for enclosure height 2000 mm. |
| Material | Cellular PU foam Flame-inhibiting to UL 94 (HF1) |
| Colour | Anthracite |
| Sealing between | Side panel and 482.6 mm (19") level |
| Dimensions | Width: 184 mm Height: 1,910 mm Depth: 84 mm |
| To fit | Width: 800 mm |
| Packs of | 1 pc(s). |
| Net weight | 0,818 kg |
| Gross weight | 0,918 kg |
| Customs tariff number | 39269097 |
| ETIM 9 | EC002620 |
| ETIM 8 | EC002620 |
| ECLASS 8.0 | 27189261 |
| Product description | SK Vertical shielding, Sealing between side panel/LCP and 482.6 mm (19") level, WHD: 184x1910x84 mm, Cellular PU foam, self-adhesive on one side |

Tender text

Thin foam rubber, 800 mm rack, vertical LCP shielding

Cellular PU foam, flame-inhibiting to UL 94 (HF1) to block the airflow on the left and right of the 82.6 mm (19 inch) level. For 800 mm wide enclosures.

Length: 1900 mm, self-adhesive

Packs of 1