

# Rittal – The System.

Faster – better – everywhere.



## SK 3322.700 Chopped-fibre filter mat

State: 20.06.2026 (Source: [rittal.com/bg-bg](http://rittal.com/bg-bg))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3322.700 - Chopped-fibre filter mat

Spare filter mats for roof-mounted fans, fan-and-filter units or thermoelectric coolers, for effective protection of enclosure components from dirt, dust and water.

## Features

|                       |  |
|-----------------------|--|
| Model No.             | SK 3322.700  |
| Design                | for filter fans  |
| Product description   | Made of chopped-fibre mat with a progressive structure. Temperature-resistant to 100 °C, self-extinguishing category F1 to DIN 53 438. Dust-laden air side: Open structure. Clean-air side: Closed structure. Reliable filtering of virtually all types of dust from a particle size of 10 µm. |
| Material              | Chemical fibres  |
| Note                  | No suitable for use in EMC filter fans.  |
| To fit Model No.      | 3238....   |
| Dimensions            | Width: 120 mm<br>Height: 120 mm<br>Depth: 11 mm  |
| Filter class          | to DIN EN 779: G2<br>to DIN EN ISO 16890: ISO Coarse 50%   |
| Packs of              | 5 pc(s).   |
| Net weight            | 0,01 kg  |
| Gross weight          | 0,013 kg   |
| Customs tariff number | 56039390   |
| ETIM 9                | EC002513   |
| ETIM 8                | EC002513   |
| ECLASS 8.0            | 27180706   |
| Product description   | SK Spare filter mat, for fan-and-filter units, for SK 3238.... WxHxD: 120 x 120 x 11 mm  |

# Approvals

---

Approvals

CSA

UR + C-UR (recognized)