

# Rittal – The System.

Faster – better – everywhere.



## SK 3342.024

# Rack-mounted fans for 482.6 mm (19")

State: 10.06.2026 (Source: [rittal.com/bg-bg](http://rittal.com/bg-bg))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3342.024 - Rack-mounted fans for 482.6 mm (19") Air throughput 320 – 480 m<sup>3</sup>/h

Rack-mounted fan for direct installation in the 482.6 mm (19") level. Installation allows air to circulate permanently inside the enclosure, thus preventing the formation of hot spots.

## Features

|                                     |  |
|-------------------------------------|--|
| Model No.                           | SK 3342.024  |
| Product description                 | Rack-mounted fan for direct installation in the 482.6 mm (19") level. Installation allows air to circulate permanently inside the enclosure, thus preventing the formation of hot spots. |
| Colour                              | RAL 7035   |
| Supply includes                     | Fully wired unit ready for connection<br>Terminal strip and assembly parts   |
| Air throughput (unimpeded air flow) | 480 m <sup>3</sup> /h  |
| Note on Model No.                   | Extended delivery times.   |
| Rated operating voltage             | 24 V (DC)  |
| Rated current max.                  | With DC: 0.74 A  |
| Pre-fuse                            | Miniature circuit-breaker/fuse: 6 A  |
| Dimensions                          | Width: 482.6 mm<br>Height: 44 mm<br>Depth: 200 mm  |
| Distance between axes of fans       | 105 mm   |
| No. of fans                         | 3  |
| Noise level                         | With DC: 51 dB(A)  |
| Operating temperature range         | -10 °C...55 °C   |
| Packs of                            | 1 pc(s).   |
| Net weight                          | 1,75 kg  |
| Gross weight                        | 1,86 kg  |

# Features

---

|                       |   |
|-----------------------|---|
| Customs tariff number | 84145915  |
| ETIM 9                | EC000320  |
| ETIM 8                | EC000320  |
| ECLASS 8.0            | 27180716  |
| Product description   | SK rack-mounted fan, for 482.6 mm (19"), 480 m <sup>3</sup> /h, 24 V (DC), WHD: 482.6 x 44 x 200 mm |

# Approvals

---

|              |                               |
|--------------|-------------------------------|
| Approvals    | UR + C-UR (recognized)<br>VDE |
| Explanations | Declaration of conformity     |