

Rittal – The System.

Faster – better – everywhere.



TS 3659.180

Server telescopic slides

State: 13.12.2025 (Source: [rittal.com/bg-bg](https://www.rittal.com/bg-bg))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TS 3659.180 - Server telescopic slides

For optimum accessibility to the servers, even when built-in.

Features

Model No.	TS 3659.180
Design	For 468.6-687.4 mm distance between levels
Product description	Facilitate optimum accessibility to the servers, even when built-in. For servers with a maximum width of 426 mm.
Material	Sheet steel
Supply includes	Telescopic slide with mounting kit Assembly parts
Extension length	511,2 mm
To fit	Enclosure type: TS: 600 mm Enclosure type: TS IT Enclosure type: VX IT
Load capacity	30 kg
Note	Only in conjunction with L-shaped mounting angles
Packs of	2 pc(s).
Net weight	2.424
Gross weight	2.624
Customs tariff number	73269098
EAN	4028177222908
ETIM 9	EC002520
ETIM 8	EC002520
ECLASS 8.0	27189261