

Rittal – The System.

Faster – better – everywhere.



HD 4000.083 Viewing window HD

State: 11.07.2026 (Source: rittal.com/bg-bg)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



HD 4000.083 - Viewing window HD

For the protection of switches or displays.

Features

Model No.	HD 4000.083
Product description	For the protection of switches or displays.
Benefits	Large viewing panel Gap-free transition between the viewing window and the frame External hinge With T handle for easy opening without a key
Material	Frame: Stainless steel 1.4301 (AISI 304) Seal: Silicone, compliant with FDA Guideline 21 CFR 177.2600 Viewing window: Polycarbonate
Supply includes	2 hinges T handle Assembly parts
Visible area	Viewing window width: 400 mm Viewing window height: 330 mm
Dimensions	Width: 518 mm Height: 436 mm Depth: 65 mm
To fit	Enclosure type: HD compact enclosure
IP protection category to IEC 60529	IP 55
IK Code	IK08
Installation options	For external mounting on surfaces.
Type rating to UL 50E	Type 1 Type 12 Type 13
Packs of	1 pc(s).
Net weight	4,15 kg

Features

Gross weight	4,206 kg
Customs tariff number	39252000
ETIM 9	EC002527
ETIM 8	EC002527
ECLASS 8.0	27182204
Product description	HD System window, with T handle, WxH: 518x436 mm, stainless steel, 1.4301
