Rittal - The System.

Faster - better - everywhere.





AS 4050.779 Wire end ferrules

State: 14.12.2025 (Source: rittal.com/bg-bg)



AS 4050.779 - Wire end ferrules loose

With plastic collar.

Features

| Model No. | AS 4050.779 |
|--------------------------|--|
| Product description | With plastic collar. |
| Technical specifications | Heat-resistant to 105 °C |
| Material | E-Cu, galvanic tin-plated Plastic collar: Polypropylene |
| Colour | Blue |
| Length | 10 mm |
| AWG | 14 |
| Internal diameter | 4,2 mm |
| Rittal colour code | Yes |
| For cross-section | 2,5 mm² |
| Note | UL-certified in conjunction with the relevant tools, such as crimping machines. For bespoke advice, please contact your Rittal sales consultant. |
| Standards | AEH DIN 46228 |
| To fit Model No. | 4051.205 4051.210 |
| Delivery form | Loose |
| Packs of | 500 pc(s). |
| Net weight | 0.5 |
| Gross weight | 0.083 |
| Customs tariff number | 85369010 |
| EAN | 4028177815704 |
| ETIM 9 | EC000005 |
| | |

© Rittal 2025

Features

| ETIM 8 | EC000005 |
|------------|----------|
| ECLASS 8.0 | 36659290 |

Approvals

| Approvals | UL + C-UL (listed) |
|-----------|--------------------|
| | UR |

© Rittal 2025 3