

**Rittal – The System.**

Faster – better – everywhere.



**AS 4050.887**

**Circular thread milling cutter**

State: 06.04.2026 (Source: [rittal.com/bg-bg](http://rittal.com/bg-bg))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4050.887 - Circular thread milling cutter

Milling cutter for cutting metric threads for Perforex machining centres BC and Perforex milling terminals MT.

## Features

|                          |   |
|--------------------------|---|
| Model No.                | AS 4050.887   |
| Product description      | Milling cutter for cutting metric threads for Perforex machining centres BC and Perforex milling terminals MT.                    |
| Technical specifications | Shaft diameter 12 mm<br>Cutting diameter 10 mm<br>Pitch 1.5 mm<br>Flank angle 60°<br>Cutting length 20 mm<br>Overall length 85 mm |
| For threads              | M12 - M64   |
| Standards                | DIN 13-1 metric ISO thread  |
| Machinable material      | Steel<br>Stainless steel<br>Cast aluminium<br>Plastic<br>Copper   |
| Packs of                 | 1 pc(s).  |
| Net weight               | 0,124 kg  |
| Gross weight             | 0,124 kg  |
| Customs tariff number    | 82077031  |
| ETIM 9                   | EC000945  |
| ETIM 8                   | EC000945  |
| ECLASS 8.0               | 36609211  |
| Product description      | Circular thread milling cutter, 10x1.5, 12 mm   |