

Rittal – The System.

Faster – better – everywhere.



AS 4051.100 Wire Station WS 540

State: 02.09.2025 (Source: rittal.com/bg-bg)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4051.100 - Wire Station WS 540

Mobile wiring workstation, height-adjustable, for flexible use in the workshop. For ergonomic, fatigue-free wire processing work.



Features

Model No.	AS 4051.100
Design	Standard
Product description	Mobile wiring workstation, height-adjustable, for flexible use in the workshop. For ergonomic, fatigue-free wire processing work.
Benefits	<ul style="list-style-type: none">Electronically adjustable desk for the optimum working height, adjustable from 710 – 1250 mmMultiplex worktop, washable and scratch-resistantIdeal solution in conjunction with the length-cutting and crimping machines plus pre-assembled wires with the Wire TerminalIntegral scale for quick manual measurementsPrepared to accommodate a monitor for wire processing with Eplan Smart WiringOptionally expandable with shelves for wire boxes, wire reels and holders for tools and small partsFor flexible use in the workshop thanks to rubberised wheelsDrawer with shadow board prepared for tools
Supply includes	<ul style="list-style-type: none">Wiring table with electrical height adjusterConnection cable, 7 m7-way socket strip, with rocker switch
Assembly instruction	The vertical mounting struts, Model No. 4051.106, are required for accessories such as storage box holders, magazine supports etc.
Input voltage	230 V AC, 50 Hz

Features

Dimensions	Width: 900 mm Height: 1,350 mm Depth: 781 mm
Working height	Working height (min.): 710 mm Working height (max.): 1,205 mm
Height adjustable y/n	Yes
Packs of	1 pc(s).
Net weight	95
Gross weight	107
Customs tariff number	94032080
EAN	4028177957480
ETIM 9	EC002224
ETIM 8	EC002224
ECLASS 8.0	21100204

Approvals

Explanations	Declaration of conformity
--------------	---------------------------