

Rittal – The System.

Faster – better – everywhere.



AS 4051.540 Wire end ferrules

State: 30.05.2026 (Source: rittal.com/bg-bg)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4051.540 - Wire end ferrules on a reel

With plastic collar.

Features

Model No.	AS 4051.540
Product description	With plastic collar.
Technical specifications	Heat-resistant to 105 °C
Material	E-Cu, galvanic tin-plated Plastic collar: Polypropylene
Colour	Orange
Length	8 mm
AWG	20
Internal diameter	2,9 mm
Rittal colour code	Yes
For cross-section	0,5 mm ²
Multinorm	Yes
Note	UL-certified in conjunction with the relevant tools, such as crimping machines.
Delivery form	Taped
Packs of	4000 pc(s).
Net weight	4 kg
Gross weight	0,465 kg
Customs tariff number	85369010
ETIM 9	EC000005
ETIM 8	EC000005
ECLASS 8.0	36659290

Features

Product description	Wire end ferrules 0.5 mm ² x 8 mm AWG 20 multinorm, packs of 4,000 pc(s)., colour: orange, delivery form: on belt (in accordance with the Rittal colour code), 0.5 mm ²
---------------------	---

Approvals

Approvals	UL + C-UL (listed)
-----------	--------------------