


# Rittal – The System.

Faster – better – everywhere.



## AS 4051.544 Wire end ferrules

State: 02.06.2026 (Source: [rittal.com/bg-bg](http://rittal.com/bg-bg))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4051.544 - Wire end ferrules on a reel

With plastic collar.

## Features

|                          |  |
|--------------------------|--|
| Model No.                | AS 4051.544  |
| Product description      | With plastic collar.   |
| Technical specifications | Heat-resistant to 105 °C   |
| Material                 | E-Cu, galvanic tin-plated<br>Plastic collar: Polypropylene   |
| Colour                   | White  |
| Length                   | 10 mm  |
| AWG                      | 20   |
| Internal diameter        | 2,9 mm   |
| For cross-section        | 0,5 mm <sup>2</sup>  |
| DIN colour code          | Yes  |
| Multinorm                | Yes  |
| Note                     | UL-certified in conjunction with the relevant tools, such as crimping machines.  |
| Delivery form            | Taped  |
| Packs of                 | 4000 pc(s).  |
| Net weight               | 4 kg   |
| Customs tariff number    | 85369010   |
| ETIM 9                   | EC000005   |
| ETIM 8                   | EC000005   |
| ECLASS 8.0               | 36659290   |
| Product description      | Wire end ferrules 0.5 mm <sup>2</sup> x 10 mm AWG 20 multinorm, packs of 4,000 pc(s)., colour: white, delivery form: on belt (in accordance with the DIN colour code), 0.5 mm <sup>2</sup> |

# Approvals

---

Approvals

UL + C-UL (listed)