

Rittal – The System.

Faster – better – everywhere.



AS 4051.551 Wire end ferrules

State: 22.06.2026 (Source: rittal.com/bg-bg)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4051.551 - Wire end ferrules on a reel

With plastic collar.

Features

Model No.	AS 4051.551
Product description	With plastic collar.
Technical specifications	Heat-resistant to 105 °C
Material	E-Cu, galvanic tin-plated Plastic collar: Polypropylene
Colour	Black
Length	8 mm
AWG	16
Internal diameter	4 mm
For cross-section	1,5 mm ²
DIN colour code	Yes
Multinorm	Yes
Note	UL-certified in conjunction with the relevant tools, such as crimping machines.
Delivery form	Taped
Packs of	4000 pc(s).
Net weight	4 kg
Gross weight	0,645 kg
Customs tariff number	85369010
ETIM 9	EC000005
ETIM 8	EC000005
ECLASS 8.0	36659290

Features

Product description	Wire end ferrules 1.5 mm ² x 8 mm AWG 16 multinorm, packs of 4,000 pc(s)., colour: black, delivery form: on belt (in accordance with the DIN colour code), 1.5 mm ²
---------------------	---

Approvals

Approvals	UL + C-UL (listed)
-----------	--------------------