

Rittal – The System.

Faster – better – everywhere.



AS 4051.600 Wire end ferrules

State: 26.05.2026 (Source: rittal.com/bg-bg)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4051.600 - Wire end ferrules on a reel

With plastic collar.

Features

Model No.	AS 4051.600
Product description	With plastic collar.
Technical specifications	Heat-resistant to 105 °C
Material	E-Cu, galvanic tin-plated Plastic collar: Polypropylene
Colour	White
Length	10 mm
AWG	18
Internal diameter	2,8 mm
Rittal colour code	Yes
For cross-section	0,75 mm ²
Note	UL-certified in conjunction with the relevant tools, such as crimping machines.
Standards	AEH DIN 46228
Delivery form	Taped
Packs of	5000 pc(s).
Net weight	5 kg
Gross weight	0,656 kg
Customs tariff number	85369010
ETIM 9	EC000005
ETIM 8	EC000005
ECLASS 8.0	36659290

Features

Product description

Wire end ferrules 0.75 mm² x 10 mm AWG 18, packs of 5,000 pc(s)., colour: white, delivery form: on belt (in accordance with the Rittal colour code)

Approvals

Approvals

UL + C-UL (listed)