

Rittal – The System.

Faster – better – everywhere.



AS 4051.695 Wire end ferrules

State: 22.06.2026 (Source: rittal.com/bg-bg)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4051.695 - Wire end ferrules on a reel

With plastic collar.

Features

Model No.	AS 4051.695
Product description	With plastic collar.
Technical specifications	Heat-resistant to 105 °C
Material	E-Cu, galvanic tin-plated Plastic collar: Polypropylene
Colour	White
Length	10 mm
AWG	20
Internal diameter	2,6 mm
For cross-section	0,5 mm ²
DIN colour code	Yes
Note	UL-certified in conjunction with the relevant tools, such as crimping machines.
Standards	AEH DIN 46228
Delivery form	Taped
Packs of	5000 pc(s).
Customs tariff number	85369010
ETIM 9	EC000005
ETIM 8	EC000005
ECLASS 8.0	36659290
Product description	Wire end ferrules 0.5 mm ² x 10 mm AWG 20, packs of 5,000 pc(s)., colour: white, delivery form: on belt (in accordance with the DIN colour code)

Approvals

Approvals

UL + C-UL (listed)