

Rittal – The System.

Faster – better – everywhere.



AS 4052.104 Screwdrivers

State: 18.06.2026 (Source: rittal.com/bg-bg)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4052.104 - Screwdrivers insulated

With a long, slender handle and high-performance tip with non-transfer insulation.

Features

Model No.	AS 4052.104
Design	Isolation protection 1000 V for slot-head screws
Product description	With a long, slender handle and high-performance tip with non-transfer insulation.
Benefits	Minimal force required, thanks to ergonomically styled handle Handle head with anti-roll protection and clear screw labelling Black coated blade tip to preserve precision and accuracy of fit Handle 30% and insulation up to 50% slimmer than comparable tools Optimum interconnection of hand and handle supports higher torques and longer, fatigue-free working
Material	Blade: Chrome-molybdenum-vanadium alloy Handle core: Hard plastic Handle body: Elastic, highly flexible plastic
Colour	Handle: Anthracite and Rittal Power Pink
Blade dia.	4 mm
Blade length	100 mm
Blade (width x thickness)	4 x 0.8 mm
Blade tip	SL
Handle dia.	25 mm
Handle length	105 mm
Standards	IEC 60 900
Packs of	3 pc(s).
Net weight	0,135
Customs tariff number	82054000

Features

ETIM 9	EC000144
ETIM 8	EC000158
ECLASS 8.0	21040406
Product description	Screwdriver insulated SL 4 x 0,8
