



# AS 4054.001 - Crimping pliers for wire end ferrules

For use with wire end ferrules with no insulating collar to DIN 46228 Part 1 and wire end ferrules with insulating collar to DIN 46228 Part 4.



## Features

Model No.	AS 4054.001
Design	Angled
Product description	For use with wire end ferrules with no insulating collar to DIN 46228 Part 1 and wire end ferrules with insulating collar to DIN 46228 Part 4.
Benefits	Minimal effort required with large wire cross-sections Uniformly high quality compression Marked die stations for precise machining of the relevant cross-sections Releasable ratchet
Material	High-quality special tool steel
Surface finish	Matt, plated
Colour	Handle: Anthracite and Rittal Power Pink
Compression	Square crimp
Direction of cable entry	Front
Dimensions	Height: 59 mm Length: 198 mm
AWG	22 - 10
For cross-section	0.5 - 6 mm <sup>2</sup>

# Features

Packs of	1 pc(s).
Net weight	0,452 kg
Gross weight	0,462 kg
Customs tariff number	82032000
ETIM 9	EC000168
ETIM 8	EC000168
ECLASS 8.0	21043811
Product description	Crimping pliers for wire end ferrules