

Rittal – The System.

Faster – better – everywhere.



AS 4054.140

Crimping pliers

State: 11.07.2025 (Source: rittal.com/bg-bg)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4054.140 - Crimping pliers for ring terminals

For use with insulated ring terminals and connectors



Features

Model No.	AS 4054.140
Design	Angled
Product description	For use with insulated ring terminals and connectors.
Benefits	Clear allocation of cross-sections, thanks to colour coding on the dies Releasable ratchet Releases as soon as the required pressure is reached, to prevent underpressing
Material	High-quality special tool steel
Surface finish	Matt, plated
Colour	Handle: Anthracite and Rittal Power Pink
Compression	Oval crimp
Dimensions	Height: 59 mm Length: 198 mm
AWG	22 - 14
For cross-section	0.75 - 2.5 mm ²
Packs of	1 pc(s).
Net weight	0.42
Gross weight	0.44

Features

Customs tariff number	82032000
EAN	4028177807686
ETIM 9	EC000168
ETIM 8	EC000168
ECLASS 8.0	21043811
