


# Rittal – The System.

Faster – better – everywhere.



## AS 4055.020

### Manual hydraulic punch

State: 16.05.2024 (Source: [rittal.com/bg-bg](https://rittal.com/bg-bg))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4055.020 - Manual hydraulic punch

For punching round, square and rectangular cut-outs



## Features

Model No.	AS 4055.020
Design	Flexible, with hydraulic hose and separate cylinder
Product description	For punching round, square and rectangular cut-outs.
Benefits	Extend tool life with a built-in overpressure valve
Material	Aluminium
Supply includes	Manual hydraulic punch Hydraulic screw Ø 19 mm Hydraulic screw Ø 9.5 / 19 mm HSS pilot drill Ø 11 mm Spacer sleeve set (3-part) Plastic case
Hydraulic operation	Round punch up to Ø 82 mm Square punch up to 68 x 68 mm Rectangular punch up to 46 x 86 mm Punching force 75 kN Max. operating pressure 680 bar/9850 psi
Packs of	1 pc(s).
Weight/pack	1,97 kg
Customs tariff number	84678900
EAN	4028177807921
ETIM 7.0	EC001085

# Features

ECLASS 8.0

21049046