

# Rittal – The System.

Faster – better – everywhere.



## AS 4055.220 Hole punch, round

State: 06.09.2025 (Source: [rittal.com/bg-bg](http://rittal.com/bg-bg))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4055.220 - Hole punch, round for sheet steel

For punching round cut-outs

## Features

Model No.	AS 4055.220
Design	With 3 cutting points
Supply includes	Female dies Male dies Tension screw without ball bearing
Machinable material	Sheet steel
Maximum machinable material thickness, sheet steel	2 mm
Ø punch	20,4 mm
For threads	M20
Note	When operating with wrenches, tension screws with ball bearings should be used. Other sizes, see splitter hole punch, round, stainless steel
Suitable for hydraulic bolt order number	4055.661
Tension screw (Ø x L)	9.5 x 50 mm
Hydraulic tension screw Ø	9,5 mm 19 mm
Packs of	1 pc(s).
Net weight	0.102
Gross weight	0.122
Customs tariff number	82073010
EAN	4028177808225
ETIM 9	EC000156
ETIM 8	EC000156

# Features

---

ECLASS 8.0

21049047