### Rittal – The System.

Faster – better – everywhere.





# SZ 4139.300 Courtesy light

State: 22.11.2025 (Source: rittal.com/bg-bg)



## SZ 4139.300 - Courtesy light

Supply voltage: 100 - 240 V AC 50/60 Hz

#### **Features**

Model No.	SZ 4139.300
Design	without door operated switch
Supply includes	Courtesy light
	Light
	Light cover
	Assembly parts
Power consumption	30 W
Ballast	Wide-range electronic ballast
Connection options	Power supply via connectors
	Door-operated switch
	Through-wiring (creating rows of lights)
Light	Fluorescent lamp, base G13
Protection class	I (PE conductor)
Switch (type)	Integral on/off/door-operated switch
Light cover	Yes
Light – installation type	Screw-fastening
Rated impulse withstand voltage, phase to earth	2000 V AC
Rated impulse withstand voltage, phase to phase	1000 V AC
Rated insulation voltage	500 V DC/1s

© Rittal 2025

#### **Features**

Installation options	TS horizontal section of the roof frame: direct
	TS, SE vertical section: with TS adaptor bracket
	SE sections at the front and rear of the roof frame: with TS adaptor
	bracket
	SE extrusions at the side of the roof frame: direct
	AE, CM, TP: with universal bracket
	AE: with rail for interior installation
Dimensions	Width: 987 mm
	Height: 117 mm
	Depth: 50 mm
Operating temperature range	-15 °C45 °C
Sockets	D, earthing-pin (type F, CEE 7/4)
Storage temperature range	-20 °C70 °C
Rated operating voltage	100 V - 240 V, 1~, 50 Hz/60 Hz
Socket version	D, earthing-pin (type F, CEE 7/4)
Packs of	1 pc(s).
Net weight	2.15
Gross weight	2.3
Customs tariff number	94054990
EAN	4028177092365
ECLASS 8.0	27189241

## Approvals

Explanations	Declaration of conformity
	Declaration of conformity UK

© Rittal 2025 3