


Rittal – The System.

Faster – better – everywhere.



PS 4338.000 Cable clamp rail

State: 23.05.2026 (Source: rittal.com/bg-bg)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



PS 4338.000 - Cable clamp rail Mounting angle for TS, PC, TP universal console, TS base/plinths

For TS, PC, TP universal console, base/plinth, for strain relief with cable entry.

Features

Model No.	PS 4338.000
Product description	For strain relief with cable entry. Depth-variable mounting on a 25 mm pitch pattern of holes on the horizontal enclosure section or in the TS base/plinth / Flex-Block.
Material	Steel
Surface finish	Zinc-plated
Supply includes	Assembly parts
Assembly instruction	The fixing bolt for base/plinths is required for mounting on the TS base/plinth
Dimensions	Length: 1,585 mm
To fit	Enclosure type: TS PC TP universal console Width: = 1,600 mm
Suitable for width	1600 mm
Packs of	2 pc(s).
Net weight	8,664 kg
Gross weight	9,12 kg
Customs tariff number	73269098
ETIM 9	EC000322
ETIM 8	EC000322
ECLASS 8.0	27400604
Product description	SZ Cable clamp rail (right angle section), for TS, PC, TP universal console, TS base/plinth, Flex-Block, for W: 1600 mm