

Rittal – The System.

Faster – better – everywhere.



VX 5301.326 Levelling feet

State: 17.04.2026 (Source: rittal.com/bg-bg)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 5301.326 - Levelling feet with internal adjustment, for VX IT

Levelling feet with internal adjustment, to compensate for floor irregularities.



Features

Model No.	VX 5301.326
Product description	The mounting bracket is used to offset and secure the levelling foot beneath the enclosure frame in the interior section. In this way, the levelling foot is conveniently adjusted from the enclosure interior using the multi-tooth drive integrated into the levelling foot shaft.
Supply includes	4 levelling feet, M12, with TX30 hex socket drive 4 mounting brackets Assembly parts
Load capacity	Max. admissible static load: 3000 N per levelling foot
Levelling range	18 - 63 mm
Packs of	4 pc(s).
Net weight	0,76 kg
Gross weight	0,796 kg
Customs tariff number	73269098
ETIM 9	EC000721
ECLASS 8.0	27182003

Features

Product description

Levelling foot, M12, with internal adjustment, for VX IT, to compensate for height differences in the event of floor irregularities, including mounting bracket to offset the mounting position in the interior section of the enclosure, for convenient adjustment from within the enclosure using the multi-tooth drive integrated into the head of the levelling foot.