Rittal – The System.

Faster – better – everywhere.



DK 5301.540 Sheet steel door, one-piece, solid

State: 04.11.2025 (Source: rittal.com/bg-bg)



POWER DISTRIBUTION CLIMATE CONTROL

DK 5301.540 - Sheet steel door, one-piece, solid for VX IT

To replace existing doors.



Features

DK 5301.540
To replace existing doors.
Sheet steel
Spray-finished
Door: RAL 7035
Comfort handle VX: RAL 9005
Door with comfort handle for semi-cylinders with security lock 3524
E
4 x 130° hinges, inside
Assembly parts
For a door opening angle of 180° when baying, a 180° baying hinge is required
Door opening angle for stand-alone siting: max. 165°
Door opening angle when baying: max. 110°
IP 55

© Rittal 2025

Features

To fit	Enclosure type: VX IT Width: = 800 mm Height: = 2,000 mm
Packs of	1 pc(s).
Net weight	31.6
Gross weight	32.6
PCF per pack (cradle-to-gate)	124.2 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
EAN	4028177955080
ETIM 9	EC000747
ECLASS 8.0	27182204

© Rittal 2025 3