

Rittal – The System.

Faster – better – everywhere.



DK 5302.035

Slide rail, 1 U, depth-variable

State: 12.05.2026 (Source: rittal.com/bg-bg)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 5302.035 - Slide rail, 1 U, depth-variable for VX IT, TE, TX CableNet

For mounting between a front and a rear pair of mounting angles.



Features

Model No.	DK 5302.035
Benefits	Tool-free, time-saving one-man assembly from the enclosure front All three mounting holes in the EIA system punchings are available for screw-fastening the equipment. Alternatively, direct screw fastening in the TE 8000 to the 482.6 mm (19") system punchings is also possible
Applications	For mounting on the front mounting level To support heavy installed equipment To adapt to individual distances between 482.6 mm (19") levels
Material	Sheet steel
Surface finish	Zinc-plated
Supply includes	Assembly parts
Installation options	482.6 mm (19") L mounting angles, front and rear 482.6 mm (19") mounting frames front and rear for 482.6 mm (19") mounting angles, standard for 482.6 mm (19") mounting angles, dynamic
Load capacity	1500 N
Note	Effective contact surface 25 mm per side

Features

To fit	Enclosure type: VX IT TE TX CableNet
Distance between levels	600 - 825 mm
Packs of	2 pc(s).
Net weight	2,86 kg
Gross weight	3,06 kg
PCF per pack (cradle-to-gate)	11.7 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	73269098
ETIM 9	EC002620
ECLASS 8.0	27189261
Product description	Slide rail, 1 U, depth-variable, for VX IT mounting angles, standard and dynamic, for TS IT L-shaped mounting angles, for TE mounting frame, for mounting on the front mounting level, load capacity 1500 N.