


**Rittal – The System.**

Faster – better – everywhere.



**DK 5302.200**

**Blanking panel, 482.6 mm (19")**

State: 08.06.2026 (Source: [rittal.com/bg-bg](http://rittal.com/bg-bg))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 5302.200 - Blanking panel, 482.6 mm (19") Tool-free attachment

Enables fast, tool-free fastening and thermal partitioning of unconfigured mounting surfaces in a 482.6 mm (19"), 1 U pitch pattern.

## Features

Model No.	DK 5302.200
Benefits	Larger areas may be covered by combining multiple units. Versatile panel for individual requirements. Extendible on both sides with additional panels. Supports multiple dismantling and reuse
Material	Plastic Fire protection corresponding to UL 94 HB, halogen-free
Surface finish	Matt
Colour	RAL 9005
Supply includes	Blanking panel, 1 U, with integral quick-fastening
Build-up height	1 U
Dimensions	Width: 482.6 mm
Units	1 U
Packs of	5 pc(s).
Net weight	0,4 kg
Gross weight	0,605 kg
PCF per pack (cradle-to-gate)	1.99 KG CO2e
Customs tariff number	73269098
ETIM 9	EC000456
ECLASS 8.0	27189217
Product description	Blanking panel, 482.6 mm (19"), 1 U, tool-free attachment, plastic, RAL 9005