

Rittal – The System.

Faster – better – everywhere.



DK 5501.320 Base mount

State: 14.05.2026 (Source: rittal.com/bg-bg)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 5501.320 - Base mount for TS IT

To accommodate gland plate modules.

Features

| | |
|-------------------------------|---|
| Model No. | DK 5501.320 |
| Product description | To accommodate gland plate modules. |
| Benefits | Tool-free mounting or screw-fastening. Easily retrofitted and combined with stabiliser. |
| Material | Sheet steel |
| Surface finish | Spray-finished |
| Colour | RAL 7035 |
| Supply includes | 2 mounting rails including assembly parts. |
| To fit | Enclosure type: TS IT TX CableNet Depth: 1,000 mm |
| Packs of | 2 pc(s). |
| Net weight | 1,6 kg |
| Gross weight | 1,92 kg |
| PCF per pack (cradle-to-gate) | 7.1 kg CO2 eq (Cat B) |
| Note on PCF category | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |
| Customs tariff number | 73269098 |
| ETIM 9 | EC002620 |
| ECLASS 8.0 | 27189261 |
| Product description | DK Base mount, 2 mounting rails incl. assembly parts, D: 1000 mm, for TS IT, TX CableNet, sheet steel, RAL 7035 |

Tender text

Base mount

For TS IT, TX CableNet

2 mounting rails, incl. assembly parts

Depth: 1000 mm

Sheet steel, RAL 7035