Rittal - The System.

Faster – better – everywhere.





DK 5501.665 Component shelf, static installation

State: 07.11.2025 (Source: rittal.com/bg-bg)



DK 5501.665 - Component shelf, static installation for VX IT, TS IT, TE, TX CableNet

For static installation between two 482.6 mm (19") mounting levels.

Features

Model No.	DK 5501.665
Benefits	Tool-free, time-saving one-man assembly
Applications	Depth-variable to adapt to individual distances between levels
Material	Sheet steel
Surface finish	Spray-finished
Colour	RAL 9005
Supply includes	Assembly parts
Installation options	482.6 mm (19") L mounting angles, front and rear 482.6 mm (19") mounting frames front and rear
Load capacity	50 kg
Dimensions	Width: 484 mm
To fit	Enclosure type: VX IT TS IT TE TX CableNet
Distance between levels	600 - 900 mm
Packs of	1 pc(s).
Net weight	6.47
Gross weight	6.62
PCF per pack (cradle-to-gate)	17.7 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	73269098

© Rittal 2025

2

Features

EAN	4028177679108
E-Number Sweden	E7239588
ETIM 9	EC002620
ECLASS 8.0	27189261

Tender text

482.6 mm (19") - component shelf, static installation Depth-variable perforated component shelf, pull-out, for L-shaped mounting angles and similar mounting angle shapes. For static installation between two 482.6 mm (19") mounting levels.

Depth-variable to adapt to individual distances between levels from 600 to 900 mm.

Tool-free, time-saving one-man assembly from the enclosure front.

Locate, pull-out, snap into position.

Perforated component shelf surface to support climate control inside the enclosure.

Load capacity 50 kg. Component shelf height 1/2 U.

Material: Sheet steel

Surface finish: Spray-finished

Colour: RAL 9005

Model No DK: 5501.665 Manufacturer: Rittal

© Rittal 2025 3