

Rittal – The System.

Faster – better – everywhere.



DK 5502.325 Drawer

State: 21.06.2026 (Source: rittal.com/bg-bg)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 5502.325 - Drawer for one 482.6 mm (19") mounting level

For front attachment to mounting angles, 482.6 mm (19"). With cover and telescopic slides to accommodate assignment lists, operating manuals and small parts.

Features

Model No.	DK 5502.325
Product description	For front attachment to mounting angles, 482.6 mm (19"). With cover and telescopic slides to accommodate assignment lists, operating manuals and small parts. The small version of the 2 U variant is also suitable for mounting inside a swing frame.
Material	Sheet steel
Colour	RAL 9005
Supply includes	Fully assembled Security lock 12321
Clearance depth	419 mm
Clearance width	411 mm
Packs of	1 pc(s).
Net weight	7,785 kg
Gross weight	8,195 kg
PCF per pack (cradle-to-gate)	31.2 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	94039910
ETIM 9	EC002620
ECLASS 8.0	27189261
Product description	DK Drawer, 3 U, For a 482.6 mm (19") attachment level, Installation depth: 427 mm, RAL 9005