## Rittal - The System.

Faster – better – everywhere.





# AX 6315.450

# Operating housing AX with handle strips

State: 10.12.2025 (Source: rittal.com/bg-bg)



## AX 6315.450 - Operating housing AX with handle strips

Operating housing with handle strips based on sheet steel AX, with support arm cut-out  $\emptyset$  130 mm to fit support arm system CP 60/120/180, service access from the front, aluminium front panel easily removable for machining, protection category IP55.







#### **Features**

| Model No.      | AX 6315.450   |
|----------------|---|
| Design         | Support arm connection Ø 130 mm                                   |
| Material       | Enclosure: Sheet steel  |
|                | Door: Sheet steel, all-round foamed-in PU seal                    |
|                | Front panel: Aluminium  |
|                | Cover caps: Plastic   |
| Surface finish | Enclosure and door: Dipcoat primed, powder-coated on the outside, |
|                | textured paint  |
|                | Handle strip: Natural anodised                                    |
|                | Front panel: Natural anodised                                     |
| General colour | RAL 7035  |
| Colour         | Enclosure and door: RAL 7035                                      |
|                | Handle strip: Natural anodised                                    |
|                | Front panel: Natural anodised                                     |
|                | Cover caps: similar to RAL 7024                                   |
|                |   |

© Rittal 2025 2

## **Features**

| Supply includes               | Enclosure with cut-out and reinforcement for support arm connection Ø 130 mm  Front with maximum cut-out, covered with easily machinable 3 mm aluminium front panel  Side handle strips with cover caps  Integral interior installation bracket with system punchings  Cam lock with 3 mm double-bit insert   |
|-------------------------------|---|
| Dimensions                    | Width: 500 mm<br>Height: 500 mm<br>Depth: 210 mm  |
| Protection category NEMA      | NEMA 1<br>NEMA 12   |
| Type rating to UL 50E         | Type 1<br>Type 12   |
| Design                        | Servicing access from the front   |
| IK Code                       | IK08  |
| Note                          | The support arm connection and door hinge may be swapped over by rotating the enclosure Optional: Support arm connection Ø 130 mm, preformed off-centre in the reinforcement plate, easily drilled out Lock systems for servicing access from the rear: Lock insert may be exchanged for mini comfort handle AX, 27 mm lock inserts, type A Lock systems for servicing access from the front: Lock insert may be exchanged for 27 mm lock inserts, type A |
| Basic material                | Sheet steel   |
| Note on Model No.             | Matching mounting panel 5051.375 with dispatch bag 5051.300   |
| Packs of                      | 1 pc(s).  |
| Net weight                    | 13  |
| Gross weight                  | 13.2  |
| PCF per pack (cradle-to-gate) | 59.6 kg CO2 eq (Cat B)  |
| Note on PCF category          | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared  |
| Customs tariff number         | 94032080  |
|                               |   |

© Rittal 2025 3

## Features

| EAN        | 4028177923201 |
|------------|---------------|
| ETIM 9     | EC002504      |
| ETIM 8     | EC002504      |
| ECLASS 8.0 | 27180505      |

## **Approvals**

| Approvals    | UL + C-UL (listed)           |
|--------------|------------------------------|
| Explanations | Declaration of conformity    |
|              | Declaration of conformity UK |

© Rittal 2025