
Rittal – The System.

Faster - better - everywhere.





State: 13.12.2025 (Source: rittal.com/hg-bg)

RITTAL

NCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROI

T INFRASTRUCTURE

VX 7030.283 - Doors for VX IT for Automatic Door Opening (ADO)

Glazed and sheet steel doors VX IT, with vent flaps for automatic opening in the event of an alarm





Features

Model No.	VX 7030.283
Design	Viewing window: Single-pane safety glass, 3 mm
	Spring damper for flap opening
	Magnets for fixing the flaps
	Valves are open at zero current
	With sheet steel door
	2-part, vertically divided, with vent flaps
	Frame: Sheet steel
Product description	With integral vent valves for automated opening function in the
	event of an alarm or power failure. The glazed door for the
	Automatic Door Opening System replaces the standard VX IT door.

© Rittal 2025

Features

Benefits	Supports remote control via the CMC III system Tinted single-pane safety glass ensures a high standard of safety Combining the vent flaps with a tubular door frame creates exceptional stability The vent flaps only protrude into the escape route by 200 mm No adjustment to the lock system required Manually opening the door has no influence on the vent flaps Automatic opening of the vent valves in the event of a power failure
Technical specifications	External projection of the vent flap: 200 mm (when opened) Internal projection of the mechanism: 52.5 mm Door hinge: right (for one-piece doors, may be swapped from right to left) Connection cable from door catch: 2.5 m
Function principle	Activation via CMC III door control module (DCM) Automatic, mechanical opening of the integral vertical ventilation flaps in an emergency if the cooling system fails or an extinguishing system is activated Depending on the room volume and temperature, the air inside the room is used for emergency cooling, or the extinguisher gas may flow directly into the IT enclosures The front and rear doors of the ADO system must always be used
Material	Frame: Sheet steel Viewing panels: Single-pane safety glass, tinted
Colour	RAL 7035
Supply includes	Door with comfort handle for semi-cylinders with security lock 3524 E
With DC	0,78 A
Dimensions	Width: 800 mm Height: 2,000 mm
IP protection category to IEC 60 529	IP 20 for solid vent flaps
Packs of	1 pc(s).
Net weight	43
Gross weight	44.5
Customs tariff number	94039910

© Rittal 2025 3

Features

EAN	4028177925953	
ETIM 9	EC002510	
ECLASS 8.0	27180101	

© Rittal 2025