# Rittal – The System.

Faster – better – everywhere.





DK 7246.400 Adaptor, 3 U

State: 19.10.2025 (Source: rittal.com/bg-bg)



## DK 7246.400 - Adaptor, 3 U Depth offset 100 mm

Used to recess 482.6 mm (19") mounting of equipment inside enclosures with 482.6 mm (19") installation in the foremost position, such as server or electronic enclosures.



#### **Features**

Model No.	DK 7246.400
Product description	This adaptor is used to recess 482.6 mm (19") mounting of equipment inside enclosures with 482.6 mm (19") installation in the foremost position, such as server or electronic enclosures. In this way, sufficient space can be gained in front of the mounting equipment to integrate patch panels or switches, whilst at the same time exploiting the maximum enclosure depth.
Material	Sheet steel
Surface finish	Zinc-plated
Supply includes	Assembly parts
Units	3 U
Installation dimensions	Installation depth for components: 482.6 mm Installation width for components: 19"
Packs of	2 pc(s).
Net weight	0.34
Gross weight	0.37
PCF per pack (cradle-to-gate)	1.4 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared

© Rittal 2025

## **Features**

Customs tariff number	83024900
EAN	4028177389830
ETIM 9	EC002625
ECLASS 8.0	27189234

## Tender text

482.6 mm (19") adaptor, 3 U, 100 mm depth offset Material: Sheet steel, zinc-plated, passivated

© Rittal 2025 3