

Rittal – The System.

Faster – better – everywhere.



DK 7320.793 Door switch

State: 23.05.2026 (Source: rittal.com/bg-bg)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7320.793 - Door switch

Switch for connecting to the normally closed contacts of the door control module for manual door opening.

Features

Model No.	DK 7320.793
Product description	Switch for connecting to the normally closed contacts of the door control module for manual door opening. For mounting on the 25 mm pitch pattern of the TS IT frame section.
Supply includes	3 m connection cable Mounting bracket Assembly parts
Installation Ø	16,2 mm
Rated voltage	250 V AC
Rated current (max.)	2 A
Packs of	1 pc(s).
Net weight	0,17 kg
Gross weight	0,178 kg
Customs tariff number	85311095
ETIM 9	EC001770
ECLASS 8.0	27390190
Product description	DK Door switch, 250 V AC, 2 A, Einbau-Ø: 16,2 mm

Approvals

Certificates	EAC
--------------	-----

Tender text

7320.793

Door switch

Button with integrated switching contact as opener. The system can be used in connection with the CMC III Door Control Module. The interruption of the contact when the button is pressed is recognised by the CMC III Door Control Module, and the solenoids are de-energised so that the door of a rack can be released and/or opened. For mounting in the LCP.

Technical specifications:

Rated voltage: 250 V AC

Rated current: max. 2 A