

Rittal – The System.

Faster – better – everywhere.



DK 7688.000

482.6 mm (19") mounting angles

State: 23.05.2026 (Source: rittal.com/bg-bg)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7688.000 - 482.6 mm (19") mounting angles for DK PS, CS New Basicgehäuse

For mounting 482.6 mm (19") components in Networking and Server Racks DK PS and in Outdoor enclosures CS New Basic

Features

| | |
|-------------------------------|--|
| Model No. | DK 7688.000 |
| Product description | For mounting 482.6 mm (19") components in DK PS network and server enclosures and in CS New Basic outdoor enclosures. The mounting angles are depth-adjustable on a 25 mm pitch pattern. A depth stay is required to attach the mounting angles. |
| Material | Sheet steel |
| Surface finish | Zinc-plated |
| Supply includes | Assembly parts |
| Units | 24 U |
| Installation dimensions | Installation depth for components: 482.6 mm Installation width for components: 19" |
| To fit | Enclosure type: CS basic enclosures DK PS Height: = 1,200 mm |
| Packs of | 2 pc(s). |
| Net weight | 2,494 kg |
| Gross weight | 2,693 kg |
| PCF per pack (cradle-to-gate) | 10.3 kg CO2 eq (Cat B) |
| Note on PCF category | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |
| Customs tariff number | 73269098 |
| ETIM 9 | EC002620 |
| ECLASS 8.0 | 27189261 |

Features

Product description

DK 482.6 mm (19") mounting angles, 24 U, For H: 1200 mm