

Rittal – The System.

Faster – better – everywhere.



DK 7831.723 Partition

State: 20.03.2026 (Source: [rittal.com/bg-bg](https://www.rittal.com/bg-bg))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7831.723 - Partition for TS IT

Partition for TS IT. For rack mounting, suspended between two TS IT enclosures.

Features

Model No.	DK 7831.723
Product description	For rack mounting, suspended between two enclosures. With 3 Ø 40 mm holes in all 4 corner areas for the insertion of cables, conduits etc. Drilled holes may be sealed with the enclosed stepped collars. For cable entry, simply cut off at a suitable level to match the required cross-section.
Material	Partition: Sheet steel Stepped collar: Plastic to UL 94-HB
Surface finish	Partition: Zinc-plated
Supply includes	12 stepped collars Ø 40 mm
To fit	Enclosure type: TS IT Height: 2,000 mm Depth: 1,000 mm
Note	Use baying connector TS 8800.490. Not suitable for use in conjunction with a baying seal. Any seals that may be present must be removed prior to installation.
Packs of	1 pc(s).
Net weight	29 kg
Gross weight	30 kg
Customs tariff number	94039910
ETIM 9	EC002525
ECLASS 8.0	27189234
Product description	DK Partition, HxD: 2000x1000 mm, For TS, TS IT, solid, zinc-plated