



# Rittal – The System.

Faster – better – everywhere.



## DK 7859.090

## PSM Zero-U-Space


State: 01.02.2026 (Source: [rittal.com/bg-bg](http://rittal.com/bg-bg))



FRIEDHELM LOH GROUP

# DK 7859.090 - PSM Zero-U-Space

Modular PDU for space-saving integration in the zero-U space between side panel and 482.6 mm (19") mounting level in 800 mm wide IT racks.



## Features

Model No.	DK 7859.090
Product description	Modular PDU for space-saving integration in the zero-U space between side panel and 482.6 mm (19") mounting level in 800 mm wide IT racks.
Material	Aluminium section, natural anodised
Length	1695 mm
Length of connection cable	3 m
Type of electrical connection	fixed/CEE
Qty.	1
Phases per infeed	1~
Rated current (max.)	32 A
Module slots (max.)	5
IP protection category to IEC 60 529	IP 20
Dimensions	Length: 1,695 mm

## Features

---

To fit	Enclosure type: VX IT Height: $\geq$ 2,000 mm
Operating temperature range	5 °C...45 °C
Ambient humidity (non-condensing)	10...90 %
Packs of	1 pc(s).
Net weight	4.9
Gross weight	5.2
Customs tariff number	85369001
EAN	4028177956643
ETIM 9	EC002762
ECLASS 8.0	27371306

---

## Approvals

---

Explanations	Declaration of conformity
--------------	---------------------------

---