



# Rittal – The System.

Faster – better – everywhere.



## VX 8168.245

## Side panel, screw-fastened, sheet steel

State: 31.07.2025 (Source: [rittal.com/bg-bg](https://www.rittal.com/bg-bg))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# VX 8168.245 - Side panel, screw-fastened, sheet steel for VX

Side panels, screw-fastened, sheet steel, for VX.

## Features

|                                      |   |
|--------------------------------------|---|
| Model No.                            | VX 8168.245   |
| Benefits                             | Time-saving assembly thanks to clip-in side panel holder<br>Automatic potential equalisation and higher EMC protection, thanks to enclosure panel holders with earthing inserts located on the inside<br>Easy positioning in the height and depth with the location aid<br>One-person assembly<br>Earthing bolts with large, paint-free contact surface for optimum contact |
| Material                             | Sheet steel, 1.5 mm   |
| Surface finish                       | Dipcoat-primed, powder-coated on the outside  |
| Colour                               | RAL 7035  |
| Supply includes                      | Assembly parts  |
| To fit                               | Enclosure type: VX<br>Height: = 1,600 mm<br>Depth: = 800 mm   |
| IP protection category to IEC 60 529 | IP 55   |
| Type rating to UL 50E                | Type 1<br>Type 12   |
| Basic material                       | Sheet steel   |
| Packs of                             | 2 pc(s).  |
| Net weight                           | 30.3  |
| Gross weight                         | 30.8  |
| PCF per pack (cradle-to-gate)        | 117.3 kg CO2 eq (Cat B)   |

# Features

|                      |  |
|----------------------|--|
| Note on PCF category | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |
| EAN                  | 4028177924949  |
| ETIM 9               | EC002524   |
| ECLASS 8.0           | 27182101   |

# Approvals

|           |                    |
|-----------|--------------------|
| Approvals | UL + C-UL (listed) |
|-----------|--------------------|