Rittal – The System.

Faster – better – everywhere.





TS 8186.235

Side panel, screw-fastened, sheet steel

State: 24.11.2025 (Source: rittal.com/bg-bg)



TS 8186.235 - Side panel, screw-fastened, sheet steel for TS, TS IT

Side panels, screw-fastened, sheet steel, for TS.

Features

Model No.	TS 8186.235	
Benefits	Automatic potential equalisation and higher EMC protection due to	
	enclosure panel holders with earthing insert	
	Easy positioning with the location aid	
	Earthing bolt with contact surface	
Material	Sheet steel, 1.5 mm	
Surface finish	Dipcoat-primed, powder-coated on the outside	
Colour	RAL 7035	
Supply includes	Assembly parts	
Note	Enclosure panel holders may optionally be fitted from the inside or	
	outside of the enclosure	
	Area available for population: External dimension – 100 mm	
To fit	Enclosure type: TS	
	TS IT	
	Height: 1,800 mm	
	Depth: 600 mm	
IP protection category to IEC 60 529	IP 55	
Basic material	Sheet steel	
Packs of	2 pc(s).	
Net weight	25	
Gross weight	26.6	
Customs tariff number	94039910	
EAN	4028177205239	

© Rittal 2025

Features

E-Number Sweden	E7282546	
ETIM 9	EC002524	
ECLASS 8.0	27182101	

Tender text

Side panels, screw-fastened, for DK TS
Easy positioning on the frame with the location aid.
The enclosure panel holders with earthing insert ensure automatic potential equalisation and higher EMC protection.

They may optionally be fitted from the inside or outside of the enclosure.
When using TS side panel hinges an opening angle of 180° is possible.

Material: 1.5 mm sheet steel

Protection category: IP 55

Surface finish: Dipcoat-primed, powder-coated in textured RAL 7035

For enclosure dimensions: H: 1800 mm D: 600 mm

© Rittal 2025 3