### Rittal – The System.

Faster – better – everywhere.





### TS 8602.060

# Base/plinth trim panels, side, 200 mm

State: 26.10.2025 (Source: rittal.com/bg-bg)



## TS 8602.060 - Base/plinth trim panels, side, 200 mm for base/plinth components front and rear

For mounting between the base/plinth components. At 200 mm height, two 100 mm base/plinth trims may be used.

#### **Features**

Model No.	TS 8602.060
Product description	For mounting between the base/plinth components. At 200 mm height, two 100 mm base/plinth trims may be used.
Material	Sheet steel
Surface finish	Spray-finished
Colour	RAL 7022
Supply includes	2 base/plinth trim panels Assembly parts
Assembly instruction	Base/plinth trim panels, side, 100 mm, may be installed rotated through 90° to stabilise bayed base/plinth components. The base/plinth baying bracket is required for this purpose
Dimensions	Height: 200 mm
To fit	Enclosure type: TS: = 600 mm  Enclosure type: SE  Enclosure type: CM  Enclosure type: TP  Enclosure type: PC  Enclosure type: IW  Enclosure type: TS IT
Packs of	2 pc(s).
Net weight	3.186
Gross weight	3.385
Customs tariff number	94039910
EAN	4028177208698

© Rittal 2025

### Features

ECLASS 8.0

27182003

© Rittal 2025 3