Rittal – The System.

Faster – better – everywhere.



TS 8610.605 Glazed door

State: 04.11.2025 (Source: rittal.com/bg-bg)



TS 8610.605 - Glazed door for TS, TS IT, VX SE

Instead of a sheet steel door or rear panel.



Features

Model No.	TS 8610.605
Product description	Instead of a sheet steel door or rear panel.
Material	Frame: Extruded aluminium section
	Corner pieces: Die-cast zinc
	Viewing window: Single-pane safety glass, 3 mm
Surface finish	Powder-coated
Colour	Frame: RAL 7035
	Corner pieces: RAL 7035
	Viewing window (printed mask on the inside): RAL 9005
Supply includes	Viewing door frame with safety glass
	Locking rod with double-bit insert
	180° hinges (4)
Visible area	Viewing window width: 460 mm
	Viewing window height: 1,840 mm
Viewing window height	1840 mm

© Rittal 2025

Features

Assembly instruction	Lock components are required when mounting instead of the rear
IP protection category to IEC 60 529	IP 55
To fit	Enclosure type: TS TS IT VX SE Width: = 600 mm Height: = 2,000 mm
Packs of	1 pc(s).
Net weight	10.5
Gross weight	12.5
EAN	4028177693845
ETIM 9	EC000747
ECLASS 8.0	27182204

© Rittal 2025 3