

Rittal – The System.

Faster – better – everywhere.



TS 8610.625 Glazed door

State: 22.05.2026 (Source: rittal.com/bg-bg)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TS 8610.625 - Glazed door for TS, TS IT, VX SE

Instead of a sheet steel door or rear panel.



Features

| | |
|-----------------------|---|
| Model No. | TS 8610.625 |
| Product description | Instead of a sheet steel door or rear panel. |
| Material | Frame: Extruded aluminium section Corner pieces: Die-cast zinc Viewing window: Single-pane safety glass, 3 mm |
| Surface finish | Powder-coated |
| Colour | Frame: RAL 7035 Corner pieces: RAL 7035 Viewing window (printed mask on the inside): RAL 9005 |
| Supply includes | Viewing door frame with safety glass Locking rod with double-bit insert 180° hinges (4) |
| Visible area | Viewing window width: 460 mm Viewing window height: 2,040 mm |
| Viewing window height | 2040 mm |

Features

| | |
|-------------------------------------|---|
| Assembly instruction | Lock components are required when mounting instead of the rear panel |
| IP protection category to IEC 60529 | IP 55 |
| To fit | Enclosure type: TS TS IT VX SE Width: = 600 mm Height: = 2,200 mm |
| Packs of | 1 pc(s). |
| Net weight | 15,7 kg |
| Gross weight | 16,2 kg |
| Customs tariff number | 76101000 |
| ETIM 9 | EC000747 |
| ECLASS 8.0 | 27182204 |
| Product description | TS Glazed door, for TS, TS IT, SE, for WH: 600x2200 mm |