


Rittal – The System.

Faster – better – everywhere.



VX 8617.060

Punched section with mounting flange, 18 x 64 mm

State: 05.06.2026 (Source: rittal.com/bg-bg)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 8617.060 - Punched section with mounting flange, 18 x 64 mm for VX

For variable, individual interior installation of the enclosure frame on the outer mounting level.



Features

| | |
|----------------------|--|
| Model No. | VX 8617.060 |
| Product description | For variable, individual interior installation of the enclosure frame on the outer mounting level. |
| Benefits | Simply locate into the system punchings from the outside and screw-fasten System punchings on all four sides With pre-bayed enclosures, the punched sections with mounting flanges may also be fitted from the inside of the enclosure |
| Material | Sheet steel |
| Surface finish | Zinc-plated |
| Supply includes | Assembly parts |
| Installation options | On the outer mounting level, on the enclosure section On the outer mounting level, between two punched sections with mounting flanges 23 x 64 mm |
| To fit | Enclosure type: VX Width/depth: 1,200 mm |
| Packs of | 4 pc(s). |

Features

| | |
|-------------------------------|---|
| Net weight | 5,3 kg |
| Gross weight | 5,46 kg |
| PCF per pack (cradle-to-gate) | 24.65 |
| Customs tariff number | 73269098 |
| ETIM 9 | EC002620 |
| ECLASS 8.0 | 27189234 |
| Product description | VX Punched section, with mounting flange 18 x 64 mm, for outer mounting level |

Approvals

| | |
|--------------|-----------------|
| Explanations | PCF-declaration |
|--------------|-----------------|