

# Rittal – The System.

Faster – better – everywhere.



## TS 8800.520 Cable duct

State: 23.05.2026 (Source: [rittal.com/bg-bg](http://rittal.com/bg-bg))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# TS 8800.520 - Cable duct for vertical TS section

For mounting on the vertical enclosure section, on two bayed enclosure sections in the vicinity of baying.



## Features

Model No.	TS 8800.520
Design	Width 50 mm, for assembly on one vertical enclosure section in the area of the side panel.
Benefits	<p>The cable duct fastening points are co-ordinated with the TS system hole pattern. This eliminates time-consuming drilling work that would be necessary with DIN ducts.</p> <p>The nominal break points of the bars are also designed for combination with the cable ducts for mounting plates.</p> <p>A further nominal break at the mounting plate height allows direct entry to the cable duct.</p>
Material	Hard PVC Flame-resistant, self-extinguishing
Colour	Similar to RAL 7030
Supply includes	Cable duct with cover
Bar width	5,5 mm
Slot width	4,5 mm
Note	Can be shortened for other enclosure sizes.

# Features

---

Dimensions	Width: 50 mm Height: 1,800 mm Depth: 80 mm
To fit	Enclosure type: TS VX SE PC IW Height: ≤ 2,000 mm
Operating temperature range	60 °C
Packs of	8 pc(s).
Net weight	9,944 kg
Gross weight	10,52 kg
Customs tariff number	39259020
ETIM 9	EC000012
ECLASS 8.0	27400703
Product description	TS Cable duct for vertical TS section, WHD: 50x1800x80 mm

---

# Approvals

---

Explanations	Declaration of conformity Declaration of conformity UK
--------------	---