

Rittal – The System.

Faster – better – everywhere.



VX 8951.030 Isolator door cover

State: 28.06.2026 (Source: rittal.com/bg-bg)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 8951.030 - Isolator door cover for VX

Including main door latch for safety locking of enclosures and bayed enclosure suites in accordance with UL regulations. Tested in conjunction with an actuator lever for master switches from the following companies: Allen Bradley, Square D, General Electric, Eaton, Siemens.

Features

Model No.	VX 8951.030
Product description	Including main door latch for safety locking of enclosures and bayed enclosure suites in accordance with UL regulations. Tested in conjunction with an actuator lever for master switches from the following companies: Allen Bradley, Square D, General Electric, Eaton, Siemens.
Benefits	<p>Meets the requirements of UL 508 A</p> <p>In conjunction with the operating mechanism, adjacent door lock and interconnecting rods, these requirements are also met for bayed combinations</p> <p>May be mounted optionally on the left or right of the enclosure. With this cover, all single-door bayed enclosures may be configured as isolator door enclosures. The complete installation surface of the enclosure is retained.</p> <p>In conjunction with the mounting plate infill, the mounting surface of the main enclosure can be enlarged by up to 14%.</p> <p>Two cut-outs for actuator levers on the front, for internal mounting at varying heights</p>

Features

Applications	<p>Allen Bradley: 1494 F-M1/P1/S1 and 140 U-K-FCX04 Square D: 9422 A1 General Electric: TDA Type 1 and 2 Eaton NZM2(3)-XSH-12-...-NA for type 4x Eaton NZM2(3)-XSH-12-...-NA for type 12 Siemens: Operating mechanism with bowden cable – complete kits 3VA9137-0CK12 for 3VA51 up to 125 A, plastic actuator, NEMA 1, 12, 3R, black=OFF, red=ON 3VA9137-0CK12 for 3VA51 up to 125 A, epoxy-coated steel actuator, NEMA 1, 12, 3R, black=OFF, red=ON 3VA9277-0CK12 for 3VA52/62 up to 250 A, plastic actuator NEMA 1, 12, 3R, black=OFF, red=ON 3VA9277-0CK12 for 3VA52/62 up to 250 A, epoxy-coated steel actuator, NEMA 1, 12, 3R, black=OFF, red=ON 3VA9477-0CK12 for 3VA53/54/63/64 up to 600 A, plastic actuator, NEMA 1, 12, 3R, black=OFF, red=ON 3VA9477-0CK12 for 3VA53/54/63/64 up to 600 A, epoxy-coated steel actuator, NEMA 1, 12, 3R, black=OFF, red=ON Siemens: Depth-variable operating mechanism – complete kits 3VA9138-0DK72, 3VA9138-0DK82, 3VA9138-0DK84 3VA9278-0DK72, 3VA9278-0DK82, 3VA9278-0DK84 3VA9478-0DK72, 3VA9478-0DK82, 3VA9478-0DK84</p>
Material	Sheet steel, 1.5 mm
Surface finish	Powder-coated
Colour	RAL 7035
Supply includes	Main door lock, cover plate and assembly parts.
Dimensions	<p>Width: 103 mm Height: 1,800 mm Depth: 500 mm</p>
Note	Cover may only be mounted on a single-door enclosure with tubular door frame
Type rating to UL 50E	<p>Type 1 Type 12</p>
Protection category to IEC 60 529	IP 55 in conjunction with enclosures from the VX series
Protection category NEMA	NEMA 12 (in conjunction with enclosures from the VX series)
Packs of	1 pc(s).

Features

Net weight	14,5 kg
Gross weight	16 kg
Customs tariff number	94039910
ETIM 9	EC000261
ECLASS 8.0	27180101
Product description	VX Isolator door cover, WHD 103x1800x500 mm

Approvals

Approvals	UL + C-UL (listed)
-----------	--------------------