

# Rittal – The System.

Faster – better – everywhere.



## SV 9340.260 OM supports

State: 30.06.2026 (Source: [rittal.com/bg-bg](http://rittal.com/bg-bg))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9340.260 - OM supports without contact system

For mounting of switchgear with external power supply.

## Features

Model No.	SV 9340.260
Design	without contact system
Product description	For mounting of switchgear with external power supply.
Material	Polyamide Fire protection corresponding to UL 94-V0
Colour	Chassis: RAL 7035
For bar systems with centre-to-centre spacing	60 mm
Support rail type	Support frame, PinBlock
Number of poles	3-pole
PinBlock	Yes
Dimensions	Width: 45 mm Height: 208 mm
To fit busbars	Height: 5, 10 mm
Support frame (W x H)	45 mm x 170 mm
Approvals	UL
Packs of	1 pc(s).
Net weight	0,219 kg
Gross weight	0,22 kg
Customs tariff number	85369095
ETIM 9	EC001166
ECLASS 8.0	27400607
Product description	SV OM Support, WH: 45x208 mm, support frame, PinBlock, without contact system

# Approvals

---

Approvals	ABS DNV Lloyds Register UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK

---

## Tender text

OM support (without contact system)  
OM support without contact system (3-pole)  
for busbar thickness 5/10 mm and PLS 800/1600  
Technical specifications  
Construction width: 55 mm  
Length: 208 mm  
Support frame: 45 x 170 mm  
Support frame support: -  
PinBlock: yes  
System:  
Rittal RiLine60